



CSGO2528140, Cold Shrink Med Volt Term Kit, 25-28kV Outdoor

By Burndy
Catalog # [CSGO2528140](#)

Cold Shrink Medium Voltage Termination Kits 25-28 kV Outdoor
Industrial Series

Features

- Length of tube is consistent before and after application
- Rip and Grip does not require heat gun or any installation tools
- Spiral rip cord design provides for easy installation with effortless unwinding providing for fast removal of the hold-out core, Rip cord is recyclable
- All kits supplied with cold shrink termination sub assembly, center end seal termination, external grounding kit, braid (without sealant), violet PVC tape, and installation guide
- Variations supplied with terminal or pin connector require customer to crimp onto conductor during installation and would require proper installation tooling
- Insulating tube offers weathering and track resistance
- Test reports available upon request

Application

To be used with Single Conductor, 25 - 28 kV XLPE and EPR copper tape, drain wire, single shield or lead sheathed power cables for the Electrical/Industrial/Construction market

Specifications

Buy American Compliant	Under Review
Environmental Conditions	Outdoor

Conductor

Conductor Range	• 5-8kV: 4/0 AWG-500 kcmil • 15kV: 1/0 AWG-250 kcmil
-----------------	--



- 25-28kV: #2-4/0 AWG

Configuration

Boot Type	NO
-----------	----

Current

Voltage Rating	25/28 kV
Phase	1-Phase

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Series	G Series
UPC	621945584495
Type	CSGO2528

Logistics

Pallet Quantity	72
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)