



CSGO3550015, Cold Shrink Med Volt Term Kit, 35kV Outdoor

By Burndy
Catalog # [CSGO3550015](#)

Cold Shrink Medium Voltage Termination Kit, 35kV Outdoor
Industrial Series



Features

- Length of tube is consistent before and after application
- Rip and Grip Does not require heat gun or any installation tools
- Spiral rip cord design provides for easy installation with effortless unwinding providing for fast removal of the hold-out core, Rip cord is recyclable
- All kits supplied with cold shrink termination sub assembly, center end seal termination, external grounding kit, braid (without sealant), violet PVC tape, and installation guide
- Variations include being supplied with terminal or pin connector, customer would crimp onto conductor during installation (terminal/pin connector do require proper installation tooling)
- Insulating tube offers weathering and track resistance
- Test reports available upon request

Application

To be used with Single Shielded Conductor, XLPE and EPR copper tape, drain wire shield, single shield or lead sheathed power cables for the Electrical/ Industrial/Construction market.

Specifications

Environmental Conditions Outdoor

Conductor

Conductor Range	• 5-8kV: 750-1000 kcmil • 15kV: 350-750 kcmil • 25-28kV: 250-500 kcmil • 35kV: 1/0 AWG-350 kcmil
-----------------	--

Configuration

Boot Type	NO
-----------	----

Current

Voltage Rating	35 kV
Phase	1-Phase

General

UPC	621945640511
Type	CSGO35
Material	Silicon Rubber

Logistics

Pallet Quantity	20
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)