



CSUDO2528140J, Cold Shrink Med Volt Termination Kit, 25-28kV Utility, Jacketed Concentric Neutral Outdoor Sleeve Only

By Burndy
Catalog # CSUDO2528140J

Medium Voltage Cold Shrink Sleeve Termination Kit, 25-28kV Utility, Jacketed Concentric Neutral Outdoor Sleeve Only

Features

- All-in-one integrated body incorporating stress control and sealant mastics
- Unique stress control system based on microvaristor (ZnO) technology that delivers exceptional discharge and impulse performance
- Quick and easy installation. Offering fewest number of steps to install
- Improved spiral rip core assembly uses smooth edges for simpler installation with less effort, heat tacked spiral core prevents unravelling during shipping and handling
- Excellent UV Resistance and hydrophobic characteristics
- Silicone Rubber body provides excellent track and erosion resistance

Specifications

Buy American Compliant	Under Review
Environmental Conditions	Outdoor

Conductor

Conductor Range	• 5-8kV: 4/0 AWG-500 kcmil • 15kV: 1/0 AWG-250 kcmil • 25-28kV: #1-4/0 AWG
-----------------	--



Configuration

Boot Type	NO
-----------	----

Current

Voltage Rating	25/28 kV
Phase	1-Phase

General

UPC	621945584761
Material	Silicone Rubber
Series	UD-JCN Series

Logistics

Pallet Quantity	72
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)