



Oh No!
IMAGE COMING SOON

CT110200SSBB, Nylon Cable Tie, 110 lb
Tensile Strength, Stainless Steel Barb, 8.7"
Long, Natural

By Burndy
Catalog # [CT110200SSBB](#)

Nylon UNIRAP™ Cable Tie - 110 Lb. Tensile Strength

Features

- Nylon 6/6 Standard
- Self-locking stainless steel barb
- Available in UV Black and Natural
- Maximum strength and adjustability for versatility
- Chemically resistant to solvents, oils, grease, and diluted acids
- Rounded edges and bent tail for easy installation
- Safe for air handling spaces
- Plenum Rated

Specifications

Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - cULus	Y
Certification - CSA Approved	Yes

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Dimension - Width mm	7 mm
Dimension - Width inch	0.28 in
Package Length	0.000 in
Package Width	0.000 in

Dimension - L Length Overall	221 mm
Dimension - Length Overall	8.7 in
Dimension - Bundle Diameter	2.01
Max inch	

Force Related

Rating - Minimum Tensile Strength lbs	110 lb
---------------------------------------	--------

General

Color	Natural
Trade Name	UNIRAP™
Series	UNIRAP™ Series
UPC	781810565360
Material	Nylon 6/6
UPC 14 Digit GTIN	00781810565360

Logistics

Pallet Quantity	1
Carton Quantity	5000

Product Assets

[Catalog \[English\]](#)