



CT110200SSBC, Nylon Tie, SS Barb, 8.7" Long, Natural

By Burndy
Catalog # [CT110200SSBC](#)

Nylon UNIRAP™ Stainless Steel Barb Cable Tie - 110 Lb. Tensile Strength

Features

- Stainless Steel Barb Tie
- Nylon 6/6, Self-locking
- Maximum strength and adjustability for versatility

Application

For use with self-locking stainless steel barb

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	No
Certification - cULus	Yes
EU RoHS Indicator	Yes
Certification - CSA Approved	Yes

Dimensions

Package Height	1.250 in
Length	8.7 in
Package Weight	0.670 lb.
Dimension - Width mm	7 mm
Dimension - Width inch	0.28 in
Package Length	14.250 in
Package Width	7.250 in
Dimension - L Length Overall mm	221 mm



Width	0.28 in
Dimension - Length Overall inch	8.70 in
Dimension - Bundle Diameter Max inch	2.01

Force Related

Rating - Minimum Tensile Strength lbs	110 lb
---------------------------------------	--------

General

Color	Natural
Trade Name	UNIRAP™
Sub Brand	UNIRAP,CABLE TIE
Series	UNIRAP™ Series
UPC	781810564769
Type	CT_SSB
Material	Nylon 6/6
UPC 14 Digit GTIN	00781810564769

Logistics

Minimum Pack Quantity	100
Pallet Quantity	15000
Carton Quantity	5000

Product Assets

[Catalog \[English\]](#)