



Oh No!
IMAGE COMING SOON

CT110225SSBC0, Nylon Cable Tie, 110 lb
Tensile Strength, Stainless Steel Barb, 9.45"
Long, Black

By Burndy
Catalog # [CT110225SSBC0](#)

Nylon 6/6 UV Stabilized Cable Tie with Stainless Steel Barb, 110
Lbs, UV Resistant Black, 2.24" Bundle Dia., Package: 100

Features

- Nylon 6/6 Standard
- Self-locking stainless steel barb
- Available in UV Black and Natural
- Maximum strength and adjustability for versatility
- Chemically resistant to solvents, oils, grease, and diluted acids
- Rounded edges and bent tail for easy installation
- Safe for air handling spaces
- Plenum Rated

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	Y
Certification - CSA Approved	Yes

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Dimension - Width mm	8 mm
Dimension - Width inch	0.32 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	240 mm
mm	

Dimension - Length Overall	9.45 in
inch	
Dimension - Bundle Diameter	2.24
Max inch	

Force Related

Rating - Minimum Tensile	113
Strength N	
Rating - Minimum Tensile	110 lb
Strength lbs	

General

Color	Black
Trade Name	UNIRAP™
UPC	781810564936
Material	Nylon 6/6
UPC 14 Digit GTIN	00781810564936

Logistics

Pallet Quantity	1
Carton Quantity	5000

Product Assets

[Catalog \[English\]](#)