



Oh No!
IMAGE COMING SOON

**CT110350SSBC, Nylon Cable Tie, 110 lb
Tensile Strength, Stainless Steel Barb,
13.78" Long, Natural**

By Burndy
Catalog # [CT110350SSBC](#)

Nylon Stainless Steel BARB Cable Ties, 13.78 IN L, .32 IN W,
Tensile Strength: 110 Lbs

Features

- Nylon 6/6 Standard
- Self-locking stainless steel barb
- Available in UV Black and Natural
- Maximum strength and adjustability for versatility
- Chemically resistant to solvents, oils, grease, and diluted acids
- Rounded edges and bent tail for easy installation
- Safe for air handling spaces
- Plenum Rated

Specifications

Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - cULus	Y
Certification - CSA Approved	Yes

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Dimension - Width mm	0 mm
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	350 mm

Dimension - Length Overall inch	13.78 in
Dimension - Bundle Diameter Max inch	3.62

Force Related

Rating - Minimum Tensile Strength N	113
Rating - Minimum Tensile Strength lbs	110 lb

General

Color	Natural
Trade Name	UNIRAP™
UPC	781810564967
Material	Nylon 6/6
UPC 14 Digit GTIN	00781810564967

Logistics

Pallet Quantity	1
Carton Quantity	2000

Product Assets

[Catalog \[English\]](#)