



**CT110400SSBC, Nylon Cable Tie,
110 lb Tensile Strength, Stainless
Steel Barb, 14.88" Long, Natural**

By Burndy
Catalog # [CT110400SSBC](#)

Nylon 6/6 Cable Tie with Stainless steel Barb, Tensile strength:
110 Lbs, Color: Natural, 14.88"L, 0.28"W, 4.02" Bundle Dia.



Oh No!
IMAGE COMING SOON

General

Catalog Number	CT110400SSBC
Color	
Material	Nylon 6/6
Rating - Minimum Tensile Strength N	113
Rating - Minimum Tensile Strength lbs	110 lb
Trade Name	UNIRAP™
UPC	781810564813

Dimensions

Dimension - Bundle Diameter Max inch	4.02
Dimension - L Length Overall mm	378 mm
Dimension - Length Overall inch	14.88 in
Dimension - Width inch	0.28 in
Dimension - Width mm	7 mm

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	2500
-----------------	------

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section G - Wire Management](#)
[Sales Drawings - 30022708](#)



A proud member of the Hubbell Family.