



CT110400SSBL, Nylon Cable Tie, 110 lb
Tensile Strength, Stainless Steel Barb,
14.88" Long, Natural

By Burndy
Catalog # [CT110400SSBL](#)

Nylon Stainless Steel BARB Cable Ties, 14.88 IN L, .28 IN W,
Tensile Strength: 110 Lbs,Material:Nylon 6/6

Features

- Nylon 6/6 Standard
- Self-locking stainless steel barb
- Available in UV Black and Natural
- Maximum strength and adjustability for versatility
- Chemically resistant to solvents, oils, grease, and diluted acids
- Rounded edges and bent tail for easy installation
- Safe for air handling spaces
- Plenum Rated

Application

For use with self-locking stainless steel barb

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	Y
EU RoHS Indicator	Yes
Certification - CSA Approved	Yes

Dimensions

Package Height	0.900 in
Package Weight	0.570 lb.
Dimension - Width mm	7 mm
Dimension - Width inch	0.28 in



Package Length	21.000 in
Package Width	6.000 in
Dimension - L Length Overall	378 mm
mm	
Dimension - Length Overall	14.88 in
inch	
Dimension - Bundle Diameter	4.02
Max inch	

Force Related

Rating - Minimum Tensile	110 lb
Strength lbs	

General

Color	Natural
Trade Name	UNIRAP™
Sub Brand	UNIRAP,CABLE TIE
UPC	781810565407
Type	CT_SSB
UPC 14 Digit GTIN	00781810565407

Logistics

Pallet Quantity	72000
Carton Quantity	3000

Product Assets

[Catalog \[English\]](#)