



**CT110400SSBLO, Nylon Cable Tie,
110 lb Tensile Strength, Stainless
Steel Barb, 14.88" Long, Black**

By Burndy
Catalog # [CT110400SSBLO](#)

Nylon Stainless Steel BARB Cable Ties, 14.88 IN L, .28 IN W,
Tensile Strength: 110 Lbs,Color:Black.



Application

For use with self-locking stainless steel barb

General

Catalog Number	CT110400SSBLO
Color	
EU RoHS Indicator	Yes
Material	Nylon 6/6
Rating - Minimum Tensile Strength lbs	110
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810565414

Dimensions

Dimension - Bundle Diameter Max inch	4.02
Dimension - L Length Overall mm	378 mm
Dimension - Length Overall inch	14.88 in
Dimension - Width inch	0.28 in
Dimension - Width mm	7 mm

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	3000
-----------------	------

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section G - Wire Management](#)
[Sales Drawings - 30022708](#)



A proud member of the Hubbell Family.