



Oh No!
IMAGE COMING SOON

**CT110600SSBC0, Nylon Cable Tie, 110 lb
Tensile Strength, Stainless Steel Barb, 21.18"
Long, Black**

By Burndy
Catalog # [CT110600SSBC0](#)

Nylon Stainless Steel BARB Cable Ties, 21.18 IN L, .28 IN W,
Tensile Strength: 110 Lbs,Max bundle dia:5.98"

Features

- Nylon 6/6 Standard
- Self-locking stainless steel barb
- Available in UV Black and Natural
- Maximum strength and adjustability for versatility
- Chemically resistant to solvents, oils, grease, and diluted acids
- Rounded edges and bent tail for easy installation
- Safe for air handling spaces
- Plenum Rated

Specifications

Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - cULus	Y
Certification - CSA Approved	Yes

Dimensions

Package Height	1.600 in
Package Weight	1.610 lb.
Dimension - Width mm	7 mm
Dimension - Width inch	0.28 in
Package Length	27.000 in
Package Width	6.750 in
Dimension - L Length Overall mm	538 mm

Dimension - Length Overall inch	21.18 in
Dimension - Bundle Diameter Max inch	5.98

Force Related

Rating - Minimum Tensile Strength N	113
Rating - Minimum Tensile Strength lbs	110 lb

General

Color	Black
Trade Name	UNIRAP™
UPC	781810564899
Material	Nylon 6/6
UPC 14 Digit GTIN	00781810564899

Logistics

Pallet Quantity	50000
Carton Quantity	2000

Product Assets

[Catalog \[English\]](#)