



CT110800SSBC, Nylon Tie, SS Barb, 27.52"
Long, Natural

By Burndy
Catalog # [CT110800SSBC](#)

Nylon UNIRAP™ Stainless Steel Barb Cable Tie - 110 Lb. Tensile Strength

Features

- Stainless Steel Barb Tie
- Nylon 6/6, Self-locking
- Maximum strength and adjustability for versatility

Application

For use with self-locking stainless steel barb

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	No
Certification - cULus	Yes
EU RoHS Indicator	Yes
Certification - CSA Approved	Yes

Dimensions

Package Height	1.750 in
Length	27.52 in
Package Weight	2.000 lb.
Dimension - Width mm	7 mm
Dimension - Width inch	0.28 in
Package Length	36.500 in
Package Width	7.500 in
Dimension - L Length Overall mm	699 mm
Width	0.28 in



Dimension - Length Overall inch	27.52 in
Dimension - Bundle Diameter Max inch	7.99

Force Related

Rating - Minimum Tensile Strength N	113
Rating - Minimum Tensile Strength lbs	110 lb

General

Color	Natural
Trade Name	UNIRAP™
Sub Brand	UNIRAP,CABLE TIE
Series	UNIRAP™ Series
UPC	781810564905
Type	CT-SSB
Material	Nylon 6/6
UPC 14 Digit GTIN	00781810564905

Logistics

Minimum Pack Quantity	100
Pallet Quantity	30000
Carton Quantity	2000

Product Assets

[Catalog \[English\]](#)