



Oh No!
IMAGE COMING SOON

**CT120300SSBC, Nylon Cable Tie, 120 lb
Tensile Strength, Stainless Steel Barb, 11.81"
Long, Natural**

By Burndy
Catalog # [CT120300SSBC](#)

Nylon Stainless Steel BARB Cable Ties, 11.81 IN L, .39 IN W, Tensile Strength: 120 Lbs,InstallationTool:MK9,TWT2

Features

- Nylon 6/6 Standard
- Self-locking stainless steel barb
- Available in UV Black and Natural
- Maximum strength and adjustability for versatility
- Chemically resistant to solvents, oils, grease, and diluted acids
- Rounded edges and bent tail for easy installation
- Safe for air handling spaces
- Plenum Rated

Specifications

Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - cULus	Y
Certification - CSA Approved	Yes

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Dimension - Width mm	10 mm
Dimension - Width inch	0.39 in
Package Length	0.000 in
Package Width	0.000 in

Dimension - L Length Overall	300 mm
Dimension - Length Overall	11.8 in
Dimension - Bundle Diameter	3.15
Max inch	

Force Related

Rating - Minimum Tensile Strength N	124
-------------------------------------	-----

General

Color	Natural
Trade Name	UNIRAP™
UPC	781810565018
Material	Nylon 6/6
UPC 14 Digit GTIN	00781810565018

Logistics

Pallet Quantity	1
Carton Quantity	3000

Product Assets

[Catalog \[English\]](#)