



**CT120300SSBL, Nylon Cable Tie, 120 lb
Tensile Strength, Stainless Steel Barb, 11.81"
Long, Natural**

By Burndy
Catalog # [CT120300SSBL](#)

Nylon Stainless Steel BARB Cable Ties, 11.81 IN L, .39 IN W, Tensile Strength: 120 Lbs,Max bundle dia:3.15"

Features

- Nylon 6/6 Standard
- Self-locking stainless steel barb
- Available in UV Black and Natural
- Maximum strength and adjustability for versatility
- Chemically resistant to solvents, oils, grease, and diluted acids
- Rounded edges and bent tail for easy installation
- Safe for air handling spaces
- Plenum Rated

Application

For use with self-locking stainless steel barb

Specifications

Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - cULus	Y
EU RoHS Indicator	Yes
Certification - CSA Approved	Yes

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Dimension - Width mm	10 mm
Dimension - Width inch	0.39 in



Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	300 mm
Dimension - Length Overall inch	11.81 in
Dimension - Bundle Diameter Max inch	3.15

Force Related

Rating - Minimum Tensile Strength lbs	120
---------------------------------------	-----

General

Color	Natural
Trade Name	UNIRAP™
Sub Brand	UNIRAP,CABLE TIE
UPC	781810643129
Type	CT_SSB
UPC 14 Digit GTIN	00781810643129

Logistics

Pallet Quantity	1
Carton Quantity	2000

Product Assets

[Catalog \[English\]](#)