



CT120400MH14LO, Tie, 4" Max Bundle, UV Black, Screw Mount

By Burndy
Catalog # [CT120400MH14LO](#)

Nylon UNIRAP™ Cable Tie - 120 Lb. Tensile Strength (Screw Mount)

Features

- Screw Mounting Hole
- Suitable for General Use

Application

For Screw Mount

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UV Rated	Yes
UL Listed	No
Certification - CSA Approved	No
Certification - 94V0 Rated	N

Configuration

Mounting Method	Screw
-----------------	-------

Dimensions

Length	16.25 in
Dimension - Width mm	8 mm
Dimension - Width inch	0.30 in
Dimension - L Length Overall mm	399 mm
Width	0.3 in
Dimension - Screw Size inch	1/4

Dimension - Length Overall inch	15.70 in
Dimension - Bundle Diameter Max inch	4.00

Force Related

Rating - Minimum Tensile Strength lbs	120
---------------------------------------	-----

General

Color	Black
Trade Name	UNIRAP™
Sub Brand	UNIRAP,CABLE TIE
Series	UNIRAP™ Series
UPC	781810335345
Type	Standard
Material	NYLON 6/6
UPC 14 Digit GTIN	00781810335345

Logistics

Carton Quantity	2000
-----------------	------

Operational

Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C

Product Assets

[Catalog \[English\]](#)



A Hubbell brand