



Oh No!
IMAGE COMING SOON

**CT120400SSBC, Nylon Cable Tie, 120 lb
Tensile Strength, Stainless Steel Barb,
15.75" Long, Natural**

By Burndy
Catalog # [CT120400SSBC](#)

Nylon Stainless Steel BARB Cable Ties, 15.75 IN L, .39 IN W,
Tensile Strength: 120 Lbs,Color:Natural

Features

- Nylon 6/6 Standard
- Self-locking stainless steel barb
- Available in UV Black and Natural
- Maximum strength and adjustability for versatility
- Chemically resistant to solvents, oils, grease, and diluted acids
- Rounded edges and bent tail for easy installation
- Safe for air handling spaces
- Plenum Rated

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	Y
Certification - CSA Approved	Yes

Dimensions

Package Height	1.700 in
Package Weight	1.780 lb.
Dimension - Width mm	0 mm
Package Length	21.500 in
Package Width	7.500 in

Dimension - L Length Overall	400 mm
Dimension - Length Overall	15.75 in
Dimension - Bundle Diameter	4.33
Max inch	

Force Related

Rating - Minimum Tensile	124
Strength N	

General

Color	Natural
Trade Name	UNIRAP™
UPC	781810565056
Material	Nylon 6/6
UPC 14 Digit GTIN	00781810565056

Logistics

Pallet Quantity	50000
Carton Quantity	2500

Product Assets

[Catalog \[English\]](#)