



Oh No!
IMAGE COMING SOON

**CT120500SSBC, Nylon Cable Tie, 120 lb
Tensile Strength, Stainless Steel Barb, 17.72"
Long, Natural**

By Burndy
Catalog # [CT120500SSBC](#)

Nylon Stainless Steel BARB Cable Ties, 17.72 IN L, .39 IN W,
Tensile Strength: 120 Lbs

Features

- Nylon 6/6 Standard
- Self-locking stainless steel barb
- Available in UV Black and Natural
- Maximum strength and adjustability for versatility
- Chemically resistant to solvents, oils, grease, and diluted acids
- Rounded edges and bent tail for easy installation
- Safe for air handling spaces
- Plenum Rated

Specifications

Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - cULus	Y
Certification - CSA Approved	Yes

Dimensions

Package Height	2.100 in
Package Weight	1.920 lb.
Dimension - Width mm	10 mm
Dimension - Width inch	0.39 in
Package Length	22.000 in
Package Width	7.500 in
Dimension - L Length Overall mm	450 mm

Dimension - Length Overall inch	17.72 in
Dimension - Bundle Diameter Max inch	4.92

Force Related

Rating - Minimum Tensile Strength N	124
Rating - Minimum Tensile Strength lbs	120 lb

General

Color	Natural
Trade Name	UNIRAP™
UPC	781810565070
Material	Nylon 6/6
UPC 14 Digit GTIN	00781810565070

Logistics

Pallet Quantity	32400
Carton Quantity	300

Product Assets

[Catalog \[English\]](#)