



Oh No!
IMAGE COMING SOON

**CT120500SSBL, Nylon Cable Tie, 120 lb
Tensile Strength, Stainless Steel Barb, 17.72"
Long, Natural**

By Burndy
Catalog # [CT120500SSBL](#)

Nylon UNIRAP™ Cable Tie - 120 Lb. Tensile Strength

Features

- Nylon 6/6 Standard
- Self-locking stainless steel barb
- Available in UV Black and Natural
- Maximum strength and adjustability for versatility
- Chemically resistant to solvents, oils, grease, and diluted acids
- Rounded edges and bent tail for easy installation
- Safe for air handling spaces
- Plenum Rated

Specifications

Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - cULus	Y
Certification - CSA Approved	Yes

Dimensions

Package Height	1.750 in
Package Weight	0.950 lb.
Dimension - Width mm	10 mm
Dimension - Width inch	0.39 in
Package Length	22.500 in
Package Width	6.000 in

Dimension - L Length Overall	450 mm
Dimension - Length Overall	17.72 in
Dimension - Bundle Diameter	4.92
Max inch	

Force Related

Rating - Minimum Tensile Strength lbs	120
---------------------------------------	-----

General

Color	Natural
Trade Name	UNIRAP™
Series	UNIRAP™ Series
UPC	781810643181
Material	Nylon 6/6
UPC 14 Digit GTIN	00781810643181

Logistics

Pallet Quantity	1300
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)