



CT175500Q, Cable Tie, 175 Lb
Tensile, Natural

By Burndy
Catalog # [CT175500Q](#)

Nylon UNIRAP - 175 Lb. Tensile Strength.



General

Catalog Number	CT175500Q
Color	
Color Code	Natural
Material	Nylon 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	32 °C
Rating - Minimum Tensile Strength N	175
Rating - Minimum Tensile Strength lbs	175
Tool Type	Heavy
Trade Name	UNIRAP
UPC	781810661093
UPC 12 Digit	7818106610933

Dimensions

Dimension - Bundle Diameter Max inch	5.5
Dimension - L Length Overall mm	460 mm
Dimension - Length Overall inch	18.10 in
Dimension - Thread Size	-
Dimension - Width inch	0.34 in
Dimension - Width mm	9 mm

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	N
Certification - cULus	N
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1000
Packaging Type	Bag

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section G - Wire Management](#)
[Sales Drawings - 50080813](#)



A proud member of the Hubbell Family.