



CT175500Q0, Cable Tie, 175 Lb Tensile, Black

By Burndy
Catalog # [CT175500Q0](#)

Nylon UNIRAP™ Cable Tie - 175 Lb. Tensile Strength

Features

- Standard Cable Tie
- Suitable for General Use
- Most sizes are available in Natural or Black

Application

For general purpose applications

Specifications

Certification - UL Recognized	Yes
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Certification - UV Rated	Yes
Certification - CSA Approved	No

Dimensions

Dimension - Width mm	8.6 mm
Dimension - Width inch	0.34 in
Dimension - L Length Overall mm	460 mm
Dimension - Length Overall inch	18.10 in
Dimension - Bundle Diameter Max inch	5.50

Force Related

Rating - Minimum Tensile Strength lbs	175
---------------------------------------	-----

General

Color	UV Black
Trade Name	UNIRAP™
Sub Brand	UNIRAP
Series	UNIRAP™ Series
Tool Type	Heavy
UPC	781810661116
Type	Cable Ties
Material	Nylon 6/6
UPC 14 Digit GTIN	00781810661116

Logistics

Minimum Pack Quantity	25
Carton Quantity	1000

Operational

Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	32 °C

Product Assets

[Catalog \[English\]](#)



A Hubbell brand