



CT175800Q0, Cable Tie, 8" Max Bundle, 175 Lb Tensile, Black

By Burndy
Catalog # [CT175800Q0](#)

Nylon UNIRAP™ Cable Tie - 175 Lb. Tensile Strength

Features

- Standard Cable Tie
- Suitable for General Use
- Most sizes are available in Natural or Black

Application

For connecting cable to ground rod

Specifications

Certification - ETL	No
Certification - UL Recognized	Yes
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	No
Certification - CSA Approved	No

Dimensions

Dimension - Width mm	8.9 mm
Dimension - Width inch	0.35 in
Dimension - L Length Overall mm	830 mm
Dimension - Length Overall inch	32.67 in
Dimension - Bundle Diameter Max inch	8.90

Force Related

Rating - Minimum Tensile Strength lbs	175
---------------------------------------	-----

General

Color	UV Black
Trade Name	UNIRAP™
Sub Brand	UNIRAP
Series	UNIRAP™ Series
Tool Type	Heavy
UPC	781810661123
Type	STANDARD
Material	NYLON 6/6
UPC 14 Digit GTIN	00781810661123

Logistics

Carton Quantity	500
-----------------	-----

Operational

Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	0 °C

Product Assets

[Catalog \[English\]](#)



A Hubbell brand