



CT175900Q, Cable Tie, 8.75" Max Bundle, 175 Lb Tensile, Natural

By Burndy
Catalog # [CT175900Q](#)

Nylon cable ties, Tensile strength-175 Lbs, Color-Natural,36.50"L, 0.34"W, 8.75" Bundle Dia.

Features

- Standard Cable Tie
- Suitable for General Use
- Most sizes are available in Natural or Black

General

Catalog Number	CT175900Q
Color	Natural
Material	NYLON 6/6
Military Specification	MS3367
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	175
Tool Type	Heavy
Trade Name	UNIRAP™
UPC	781810333747
UPC 14 Digit GTIN	00781810333747

Dimensions

Dimension - Bundle Diameter Max inch	8.75
Dimension - L Length Overall mm	927 mm
Dimension - Length Overall inch	36.50 in
Dimension - Width inch	0.34 in



Dimension - Width mm	8.6 mm
----------------------	--------

Certifications And Compliance

Certification - 94V0 Rated	N
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - UV Rated	No
Certification - cULus	No
Industry Standard(s)	Military Specified (Mil-Spec)
Military Spec Number	MS3367-6-9
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	500
Minimum Pack Quantity	25
Packaging Type	Bag

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_CT_UNIRAP_CABLE_TIE_LineArt](#)
[Sales Drawings - 50080813](#)
[Specifications - CT175900Q](#)



A Hubbell brand