



CT18075IDC, Tie, .75" Max Bundle, Natural, Identification

By Burndy
Catalog # [CT18075IDC](#)

Nylon UNIRAP™ Cable Tie - 18 Lb. Tensile Strength (Identification), 100 pack



Features

- Identification

Specifications

Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
Certification - UV Rated	No
Industry Standard(s)	Military Specified (Mil-Spec)
Certification - CSA Approved	No
Military Spec Number	MS3368-5-E
Certification - 94V0 Rated	N

Dimensions

Package Height	0.750 in
Length	4.01 in
Package Weight	0.110 lb.
Dimension - Width mm	2.5 mm
Dimension - Width inch	0.10 in
Package Length	8.500 in
Package Width	5.250 in
Dimension - L Length Overall mm	104 mm
Dimension - Marking Pad Size inch	0.33 X 1.00
Width	0.1 in
Dimension - Length Overall inch	4.10 in

Dimension - Bundle Diameter Max inch	0.75
--------------------------------------	------

Force Related

Rating - Minimum Tensile Strength lbs	18
---------------------------------------	----

General

Color	Natural
Trade Name	UNIRAP™
Series	UNIRAP™ Series
UPC	781810335369
Material	Nylon 6/6
Military Specification	MS3368
UPC 14 Digit GTIN	00781810335369

Logistics

Minimum Pack Quantity	100
Pallet Quantity	99999
Carton Quantity	1000
Packaging Type	Bag

Operational

Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C

Product Assets

[Catalog \[English\]](#)