



CT18087SSBM, Nylon Cable Tie, 18 lb  
Tensile Strength, Stainless Steel Barb, 3.94"  
Long, Natural

By Burndy  
Catalog # CT18087SSBM

Nylon UNIRAP™ Cable Tie - 18 Lb. Tensile Strength

Features

- Nylon 6/6 Standard
- Self-locking stainless steel barb
- Available in UV Black and Natural
- Maximum strength and adjustability for versatility
- Chemically resistant to solvents, oils, grease, and diluted acids
- Rounded edges and bent tail for easy installation
- Safe for air handling spaces
- Plenum Rated

Specifications

|                              |     |
|------------------------------|-----|
| Certification - ETL          | No  |
| Standards - RoHS Compliance  | CM  |
| Status                       |     |
| Certification - cULus        | Y   |
| Certification - CSA Approved | Yes |

Dimensions

|                        |           |
|------------------------|-----------|
| Package Height         | 0.000 in  |
| Package Weight         | 0.000 lb. |
| Dimension - Width mm   | 3 mm      |
| Dimension - Width inch | 0.12 in   |
| Package Length         | 0.000 in  |
| Package Width          | 0.000 in  |



Oh No!  
IMAGE COMING SOON

|                              |         |
|------------------------------|---------|
| Dimension - Length Overall   | 3.94 in |
| inch                         |         |
| Dimension - L Length Overall | 100 mm  |
| mm                           |         |
| Dimension - Bundle Diameter  | 0.87 in |
| Max inch                     |         |

Force Related

|                          |       |
|--------------------------|-------|
| Rating - Minimum Tensile | 18 lb |
| Strength lbs             |       |

General

|            |                |
|------------|----------------|
| Color      | Natural        |
| UPC        | 781810565131   |
| Trade Name | UNIRAP™        |
| Material   | Nylon 6/6      |
| Series     | UNIRAP™ Series |

Logistics

|                 |      |
|-----------------|------|
| Pallet Quantity | 1    |
| Carton Quantity | 3000 |

Product Assets

[Catalog \[English\]](#)