



Oh No!
IMAGE COMING SOON

CT40137SSBM, Nylon Cable Tie, 40 lb
Tensile Strength, Stainless Steel Barb, 5.91",
Natural

By Burndy
Catalog # [CT40137SSBM](#)

Nylon UNIRAP™ Cable Tie - 40 Lb. Tensile Strength

Features

- Nylon 6/6 Standard
- Self-locking stainless steel barb
- Available in UV Black and Natural
- Maximum strength and adjustability for versatility
- Chemically resistant to solvents, oils, grease, and diluted acids
- Rounded edges and bent tail for easy installation
- Safe for air handling spaces
- Plenum Rated

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	Y
Certification - CSA Approved	Yes

Dimensions

Package Height	1.400 in
Package Weight	1.460 lb.
Dimension - Width mm	3 mm
Dimension - Width inch	0.14 in
Package Length	13.750 in
Package Width	9.000 in

Dimension - L Length Overall	150 mm
Dimension - Length Overall	5.91 in
Dimension - Bundle Diameter	1.38
Max inch	

Force Related

Rating - Minimum Tensile	40 lb
Strength lbs	

General

Color	Natural
Trade Name	UNIRAP™
Series	UNIRAP™ Series
UPC	781810565155
Material	Nylon 6/6
UPC 14 Digit GTIN	00781810565155

Logistics

Pallet Quantity	99999
Carton Quantity	3000

Product Assets

[Catalog \[English\]](#)



A Hubbell brand