



CT40200SSBD, Nylon Cable Tie, 40 lb Tensile Strength, Stainless Steel Barb, 7.87" Long, Natural

By Burndy
Catalog # [CT40200SSBD](#)

Nylon Stainless Steel BARB Cable Ties, 7.87 IN L, .15 IN W, Tensile Strength: 40 Lbs.



Application

For use with self-locking stainless steel barb

General

Catalog Number	CT40200SSBD
Color	
EU RoHS Indicator	Yes
Material	Nylon 6/6
Rating - Minimum Tensile Strength lbs	40 lb
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT-SSB
UPC	781810565216

Dimensions

Dimension - Bundle Diameter Max inch	1.97
Dimension - L Length Overall mm	200 mm
Dimension - Length Overall inch	7.87 in
Dimension - Width inch	0.15 in
Dimension - Width mm	4 mm

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	3000
-----------------	------

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section G - Wire Management](#)
[Sales Drawings - 30022708](#)



A proud member of the Hubbell Family.