



**CT40300SSBD, Nylon Cable Tie,
40 lb Tensile Strength, Stainless
Steel Barb, 11.81" Long, Natural**

By Burndy
Catalog # [CT40300SSBD](#)

Nylon Stainless Steel BARB Cable Ties, 11.18 IN L, .14 IN W,
Tensile Strength: 40 Lbs.



Application

For use with self-locking stainless steel barb

General

Catalog Number	CT40300SSBD
Color	
EU RoHS Indicator	Yes
Material	Nylon 6/6
Rating - Minimum Tensile Strength lbs	40 lb
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810565179

Dimensions

Dimension - Bundle Diameter Max inch	3.15
Dimension - L Length Overall mm	284 mm
Dimension - Length Overall inch	11.18 in
Dimension - Width inch	0.14 in
Dimension - Width mm	3 mm

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	8000
-----------------	------

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section G - Wire Management](#)
[Sales Drawings - 30022708](#)



A proud member of the Hubbell Family.