



CT40400SSBC, Nylon Tie, SS Barb, 14.49" Long, Natural

By Burndy
Catalog # [CT40400SSBC](#)

Nylon UNIRAP™ Stainless Steel Barb Cable Tie - 40 Lb. Tensile Strength

Features

- Stainless Steel Barb Tie
- Nylon 6/6, Self-locking
- Maximum strength and adjustability for versatility

Application

For use with self-locking stainless steel barb

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	No
Certification - cULus	Yes
EU RoHS Indicator	Yes
Certification - CSA Approved	Yes

Dimensions

Package Height	0.880 in
Length	14.49 in
Package Weight	0.400 lb.
Dimension - Width mm	3 mm
Dimension - Width inch	0.14 in
Package Length	19.000 in
Package Width	4.250 in
Dimension - L Length Overall mm	368 mm



Width	0.14 in
Dimension - Length Overall inch	14.49 in
Dimension - Bundle Diameter Max inch	4.09

Force Related

Rating - Minimum Tensile Strength lbs	40 lb
---------------------------------------	-------

General

Color	Natural
Trade Name	UNIRAP™
Sub Brand	UNIRAP,CABLE TIE
Series	UNIRAP™ Series
UPC	781810564561
Type	CT_SSB
Material	Nylon 6/6
UPC 14 Digit GTIN	00781810564561

Logistics

Minimum Pack Quantity	100
Pallet Quantity	4000
Carton Quantity	8000

Product Assets

[Catalog \[English\]](#)