



CT40400SSBD0, Nylon Cable Tie, 40 lb
Tensile Strength, Stainless Steel Barb,
14.49" Long, Black

By Burndy
Catalog # [CT40400SSBD0](#)

Nylon UNIRAP™ Cable Tie - 40 Lb. Tensile Strength

Features

- Nylon 6/6 Standard
- Self-locking stainless steel barb
- Available in UV Black and Natural
- Maximum strength and adjustability for versatility
- Chemically resistant to solvents, oils, grease, and diluted acids
- Rounded edges and bent tail for easy installation
- Safe for air handling spaces
- Plenum Rated

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	Y
Certification - CSA Approved	Yes

Dimensions

Package Height	2.000 in
Package Weight	1.870 lb.
Dimension - Width mm	3 mm
Dimension - Width inch	0.14 in
Package Length	19.000 in
Package Width	9.000 in



Dimension - L Length Overall	368 mm
Dimension - Length Overall	14.49 in
Dimension - Bundle Diameter	4.09
Max inch	

Force Related

Rating - Minimum Tensile	40 lb
Strength lbs	

General

Color	Black
Trade Name	UNIRAP™
Series	UNIRAP™ Series
UPC	781810565209
Material	Nylon 6/6
UPC 14 Digit GTIN	00781810565209

Logistics

Pallet Quantity	99999
Carton Quantity	8000

Product Assets

[Catalog \[English\]](#)