



# CT50175IDC, Tie, 1.81" Max Bundle, Natural, Identification

By Burndy  
Catalog # [CT50175IDC](#)

Nylon UNIRAP™ Cable Tie - 50 Lb. Tensile Strength (Identification), 100 pack



### Features

- Identification

### Specifications

|                                    |                               |
|------------------------------------|-------------------------------|
| Standards - Industry Standards Met | Military Specified (Mil-Spec) |
| Standards - RoHS Compliance Status | CM                            |
| Certification - UV Rated           | No                            |
| Industry Standard(s)               | Military Specified (Mil-Spec) |
| Certification - CSA Approved       | No                            |
| Military Spec Number               | MS3368-1-A                    |
| Certification - 94V0 Rated         | N                             |

### Dimensions

|                                   |           |
|-----------------------------------|-----------|
| Package Height                    | 1.250 in  |
| Length                            | 7.91 in   |
| Package Weight                    | 0.340 lb. |
| Dimension - Width mm              | 5 mm      |
| Dimension - Width inch            | 0.18 in   |
| Package Length                    | 12.750 in |
| Package Width                     | 5.250 in  |
| Dimension - L Length Overall mm   | 201 mm    |
| Dimension - Marking Pad Size inch | 1 X 7/16  |
| Width                             | 0.18 in   |
| Dimension - Length Overall inch   | 7.91 in   |

|                                      |         |
|--------------------------------------|---------|
| Dimension - Bundle Diameter Max inch | 1.81 in |
|--------------------------------------|---------|

### Force Related

|                                       |    |
|---------------------------------------|----|
| Rating - Minimum Tensile Strength lbs | 50 |
|---------------------------------------|----|

### General

|                        |                |
|------------------------|----------------|
| Color                  | Natural        |
| Trade Name             | UNIRAP™        |
| Series                 | UNIRAP™ Series |
| UPC                    | 781810335383   |
| Material               | Nylon 6/6      |
| Military Specification | MS3368         |
| UPC 14 Digit GTIN      | 00781810335383 |

### Logistics

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 1000  |
| Pallet Quantity       | 99999 |
| Carton Quantity       | 1000  |
| Packaging Type        | Bag   |

### Operational

|                                   |        |
|-----------------------------------|--------|
| Operating Temperature Celcius Max | 85 °C  |
| Operating Temperature Celcius Min | -40 °C |

### Product Assets

[Catalog \[English\]](#)