



CT50175MH10C0, Tie, 1.75" Max Bundle, UV Black, Screw Mount

By Burndy
Catalog # [CT50175MH10C0](#)

Nylon UNIRAP™ Cable Tie - 50 Lb. Tensile Strength (Screw Mount), 100 pack



Features

- Screw Mounting Hole
- Suitable for General Use

Application

For Screw Mount

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	Yes
EU RoHS Indicator	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - UV Rated	Yes
UL Listed	No
Certification - CSA Approved	No
Certification - 94V0 Rated	N

Configuration

Mounting Method	Screw
-----------------	-------

Dimensions

Package Height	1.100 in
Package Weight	0.360 lb.
Package Length	13.000 in
Package Width	6.000 in
Dimension - L Length Overall mm	203 mm
Width	0.18 in
Dimension - Screw Size inch	#10
Length	8.5 in

Dimension - Width mm	4 mm
Dimension - Width inch	0.17 in
Dimension - Length Overall inch	8.00 in
Dimension - Bundle Diameter Max inch	1.75 in

Force Related

Rating - Minimum Tensile Strength lbs	50
---------------------------------------	----

General

Trade Name	UNIRAP™
Color	Black
Sub Brand	UNIRAP,CABLE TIE
Series	UNIRAP™ Series
UPC	781810335260
Type	Standard
Material	Nylon 6/6
UPC 14 Digit GTIN	00781810335260

Logistics

Minimum Pack Quantity	100
Pallet Quantity	99999
Carton Quantity	5000

Operational

Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C

Product Assets

[Catalog \[English\]](#)