



BURNDY

CT50250SSBC, Nylon Cable Tie, 50 lb Tensile Strength, Stainless Steel Barb, 9.84" Long, Natural

By Burndy

Catalog # [CT50250SSBC](#)

Nylon Stainless Steel BARB Cable Ties, 9.84 IN L, .19 IN W, Tensile Strength: 50 Lbs, Material: Nylon 6/6



Features

- Nylon 6/6 Standard
- Self-locking stainless steel barb
- Available in UV Black and Natural
- Maximum strength and adjustability for versatility
- Chemically resistant to solvents, oils, grease, and diluted acids
- Rounded edges and bent tail for easy installation
- Safe for air handling spaces
- Plenum Rated

Application

For use with self-locking stainless steel barb

Specifications

Certification - ETL

No

Standards - RoHS Compliance Status

CM

Certification - cULus

Y

EU RoHS Indicator

Yes

Certification - CSA Approved

Yes

Dimensions

Package Height

1.600 in

Package Weight

1.060 lb.

Dimension - Width mm

5 mm

Dimension - Width inch

0.19 in

Package Length

16.250 in

Package Width

7.500 in

Dimension - L Length Overall mm

250 mm

Dimension - Length Overall inch

9.84 in

Dimension - Bundle Diameter Max inch

2.56

Force Related

Rating - Minimum Tensile Strength lbs

50

General

Color

Natural

Trade Name

UNIRAP™

Sub Brand

UNIRAP,CABLE TIE

UPC

781810564639

Type

CT_SSB

UPC 14 Digit GTIN

00781810564639

Logistics

Pallet Quantity

99999

Carton Quantity

6001

Product Assets

[Catalog \[English\]](#)



A Hubbell brand
© 2026 Hubbell Incorporated. All rights reserved
BRDY_CA-CT50250SSBC-SPEC-EN | REV 5/2026