




CT50300M0, Tie, 1.25" Max Bundle, 30 Lb Tensile, UV Black

By Burndy
Catalog # [CT50300M0](#)

Nylon UNIRAP™ Cable Tie - 50 Lb. Tensile Strength



Features

- Standard Cable Tie
- Suitable for General Use
- Most sizes are available in Natural or Black

Application

For Outdoor Applications

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UV Rated	Yes
Industry Standard(s)	Military Specified (Mil-Spec)
UL Listed	No
Certification - CSA Approved	No
Military Spec Number	MS3367-7-0
Certification - 94VO Rated	N

Dimensions

Length	11.75 in
Dimension - Width mm	5 mm
Dimension - Width inch	0.18 in
Dimension - L Length Overall mm	282 mm
Width	0.18 in

Dimension - Length Overall inch	11.1 in
Dimension - Bundle Diameter Max inch	3

Force Related

Rating - Minimum Tensile Strength lbs	50
---------------------------------------	----

General

Color	Black
Trade Name	UNIRAP™
Sub Brand	UNIRAP,CABLE TIE
Series	UNIRAP™ Series
UPC	781810332894
Type	Standard
Material	NYLON 6/6
Military Specification	MS3367
UPC 14 Digit GTIN	00781810332894

Logistics

Carton Quantity	5000
-----------------	------

Operational

Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C

Product Assets

[Catalog \[English\]](#)