



CT50400M0, Cable Tie, 4" Max Bundle, 50 Lb Tensile, UV Black 1

By Burndy
Catalog # [CT50400M0](#)

UV Black1 Nylon 6/6 Cable Tie, 4" Max. Bundle Dia, 50 Lbs, 15.50" Long, 0.18" Wide.



General

Application	For Outdoor Applications
Catalog Number	CT50400M0
Color	Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	50
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	Standard
UPC	781810332917

Dimensions

Dimension - Bundle Diameter Max inch	4
Dimension - L Length Overall mm	362 mm
Dimension - Length Overall inch	14.25 in
Dimension - Width inch	0.18 in
Dimension - Width mm	5 mm

Certifications And Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Military Spec Number	MS3367-2-0
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	5000
-----------------	------

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CT_UNIRAP_CABLE_TIE_LineArt](#)
- [Sales Drawings - 50080813](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_MX-CT50400M0-SPEC-EN | REV 6/2024