



CT50400MH10C0, Cable Tie, 4"

Max Bundle, 50 Lb Tensile, UV Black, Screw Mount

By Burndy
Catalog # [CT50400MH10C0](#)

Nylon cable ties, Tensile strength-50 Lbs, Color- UV Black, 14.50"L, 0.17"W, 04.00" Bundle Dia.

Features

- Screw Mounting Hole
- Suitable for General Use

Application

Bundling and mounting, one easy installation. Ideal for use where bundle needs to be secured, such as control panels and ceilings

General

Catalog Number	CT50400MH10C0
Color	Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Mounting Method	Screw
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	50
Sub Brand	UNIRAP
Trade Name	UNIRAP™
Type	CT-MH
UPC	781810335307
UPC 14 Digit GTIN	00781810335307

Dimensions

Dimension - Bundle Diameter Max inch	4
Dimension - L Length Overall mm	368 mm



Dimension - Length Overall inch	14.50 in
Dimension - Screw Size inch	#10
Dimension - Width inch	0.18 in
Dimension - Width mm	5 mm
Length	15.25 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - 94V0 Rated	N
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	Yes
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Packaging Type	Bag

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_CT_MH_UNIRAP_CABLE_TIE_LineArt](#)
[Sales Drawings - 50080813](#)
[Specifications - CT50400MH10C0](#)



A Hubbell brand