



CTB075AA4C, Cable Tie Mounting Base, Acrylic Adhesive

By Burndy
Catalog # [CTB075AA4C](#)

Nylon UNIRAP™ Cable Tie Mounting Base, Natural, .74"x.74", Max Tie Slot Width .20", 100 pack



Features

- Cable Tie Base

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Certification - UV Rated	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Mounting Method	Acrylic adhesive or #4 screw
-----------------	------------------------------

Dimensions

Package Height	0.500 in
Length	0.74 in
Package Weight	0.180 lb.
Dimension - Width inch	0.74 in
Package Length	8.750 in
Package Width	6.100 in
Dimension - B Length inch	0.74 in
Height	0.19 in

Width	0.74 in
Dimensions	0.74 in x 0.74 in x 0.19 in

General

Color	Natural
Trade Name	UNIRAP™
Series	UNIRAP™ Series
UPC	781810335765
Type	Cable Tie Bases
Material	Nylon 6/6
UPC 14 Digit GTIN	00781810335765

Logistics

Minimum Pack Quantity	100
Pallet Quantity	99999
Carton Quantity	1000
Packaging Type	Bag

Operational

Operating Temperature Celcius	70 °C
Max	
Operating Temperature Celcius	0 °C
Min	

Product Assets

[Catalog \[English\]](#)