



CTB075AA4M, Mounting Base, Acrylic Adhesive, Natural

By Burndy
Catalog # [CTB075AA4M](#)

Nylon UNIRAP™ Cable Tie Mounting Bases, Acrylic Adhesive, Natural Color, Max Tie Slot Width .14", 1000 pack



Features

- Cable Tie Base

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UV Rated	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Mounting Method	Acrylic adhesive or #6 or #8 Screw
-----------------	------------------------------------

Dimensions

Length	0.75 in
Dimension - Width inch	0.75 in
Dimension - B Length inch	0.75 in
Height	0.19 in

Width	0.75 in
Dimensions	0.75 in x 0.75 in x 0.19 in

General

Color	Natural
Series	UNIRAP™ Series
UPC	781810335789
Type	Cable Tie Bases
Material	Nylon 6/6
UPC 14 Digit GTIN	00781810335789

Logistics

Minimum Pack Quantity	10000
Packaging Type	Bag

Operational

Operating Temperature Celcius Max	70 °C
Operating Temperature Celcius Min	0 °C

Product Assets

[Catalog \[English\]](#)