



CTB075RA4C, Mounting Base, Rubber Adhesive, Natural

By Burndy
Catalog # [CTB075RA4C](#)

Nylon UNIRAP™ Cable Tie Mounting Bases, Rubber Adhesive, .14"
Max Tie Slot Width, 100 pack



Features

- Cable Tie Base
- Rubber Adhesive Mounting

Application

For used in conjunction with cable ties to stabilize and secure wire bundles

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - UV Rated	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Mounting Method	Rubber adhesive or #4 screw
-----------------	-----------------------------

Dimensions

Package Height	0.500 in
Package Weight	0.180 lb.
Package Length	8.500 in
Package Width	5.900 in

Width	0.99 in
Length	0.99 in
Dimension - Width inch	0.74 in
Dimension - B Length inch	0.74 in
Height	0.2 in
Dimensions	0.99 in x 0.99 in x 0.2 in

General

Trade Name	UNIRAP™
Color	Natural
Sub Brand	UNIRAP,CABLE TIE
Series	UNIRAP™ Series
UPC	781810335802
Type	Cable Tie Bases
Material	Nylon 6/6
UPC 14 Digit GTIN	00781810335802

Logistics

Minimum Pack Quantity	100
Pallet Quantity	99999
Carton Quantity	1000

Operational

Operating Temperature Celcius	70 °C
Max	
Operating Temperature Celcius	0 °C
Min	

Product Assets

[Catalog \[English\]](#)