



# CTB075RA4M, Mounting Base, Rubber Adhesive, Natural

By Burndy  
Catalog # [CTB075RA4M](#)

Nylon UNIRAP™ Cable Tie Mounting Bases, Rubber Adhesive, Natural Color, Max Tie Slot Width .20", 1000 pack



## Features

- Cable Tie Base

## Specifications

|                               |     |
|-------------------------------|-----|
| Certification - ETL           | No  |
| Certification - UL Recognized | Yes |
| Standards - RoHS Compliance   | CM  |
| Status                        |     |
| Certification - cULus         | No  |
| Certification - UV Rated      | No  |
| UL Listed                     | No  |
| Certification - CSA Approved  | No  |

## Configuration

|                 |                             |
|-----------------|-----------------------------|
| Mounting Method | Rubber adhesive or #4 screw |
|-----------------|-----------------------------|

## Dimensions

|                           |           |
|---------------------------|-----------|
| Package Height            | 0.000 in  |
| Length                    | 0.75 in   |
| Package Weight            | 0.000 lb. |
| Dimension - Width inch    | 0.74 in   |
| Package Length            | 0.000 in  |
| Package Width             | 0.000 in  |
| Dimension - B Length inch | 0.74 in   |
| Height                    | 0.19 in   |

|            |                             |
|------------|-----------------------------|
| Width      | 0.75 in                     |
| Dimensions | 0.75 in x 0.75 in x 0.19 in |

## General

|                   |                 |
|-------------------|-----------------|
| Color             | Natural         |
| Trade Name        | UNIRAP™         |
| Series            | UNIRAP™ Series  |
| UPC               | 781810335826    |
| Type              | Cable Tie Bases |
| Material          | Nylon 6/6       |
| UPC 14 Digit GTIN | 00781810335826  |

## Logistics

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 1000 |
| Pallet Quantity       | 1    |
| Carton Quantity       | 1000 |
| Packaging Type        | Bag  |

## Operational

|                               |       |
|-------------------------------|-------|
| Operating Temperature Celcius | 70 °C |
| Max                           |       |
| Operating Temperature Celcius | 0 °C  |
| Min                           |       |

## Product Assets

[Catalog \[English\]](#)