



CTB075S4M, Cable Tie Mounting Base, Screw Mount, Natural

By Burndy
Catalog # [CTB075S4M](#)

Nylon UNIRAP™ Cable Tie Mounting Base, Natural, .74"x.74", .2"
Max Tie Slot Width, 1000 pack



Features

- Cable Tie Base

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Certification - UV Rated	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Mounting Method	#4 screw
-----------------	----------

Dimensions

Package Height	0.000 in
Length	0.74 in
Package Weight	0.000 lb.
Dimension - Width inch	0.74 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	0.74 in
Height	0.19 in

Width	0.75 in
Dimensions	0.74 in x 0.75 in x 0.19 in

General

Color	Natural
Series	UNIRAP™ Series
UPC	781810335741
Type	Cable Tie Bases
Material	Nylon 6/6
UPC 14 Digit GTIN	00781810335741

Logistics

Minimum Pack Quantity	10000
Pallet Quantity	1
Carton Quantity	1000
Packaging Type	Bag

Operational

Operating Temperature Celcius	70 °C
Max	
Operating Temperature Celcius	0 °C
Min	

Product Assets

[Catalog \[English\]](#)