




CTNT50200D0, Tie, 2" Max Bundle, Black, Nylon 12

By Burndy
Catalog # [CTNT50200D0](#)



Nylon 12 UNIRAP™ Cable Tie - 50 Lb. Tensile Strength

Features

- Nylon 12 Cable Ties provide excellent UV, chemical and moisture resistant
- Ties feature inside serrations and bent tail for quick, easy installation
- Smooth edge to prevent bundle damage
- Especially suitable in high moisture, corrosive (zinc chloride and dilute acids) environments
- Good in low temperatures
- Indoor/Outdoor applications

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No

Dimensions

Width	0.19 in
Length	7.5 in
Thickness	0.05 in
Dimension - Width mm	4.8 mm
Dimension - Width inch	0.19 in
Dimension - Length Overall inch	7.50 in

Dimension - L Length Overall mm	190 mm
Dimension - Bundle Diameter Max inch	2.00 in

Force Related

Tensile Strength	50 / 22 lb./Kg
Rating - Minimum Tensile Strength lbs	50 lb

General

Color	Black
UPC	621945469426
Trade Name	UNIRAP™
Material	Nylon 12
Series	UNIRAP™ Series

Logistics

Minimum Pack Quantity	500
Carton Quantity	15000

Product Assets

[Catalog \[English\]](#)