




CTNT50725C0, Tie, 7.3" Max Bundle, Black, Nylon 12

By Burndy
Catalog # [CTNT50725C0](#)



Nylon 12 UNIRAP™ Cable Tie - 50 Lb. Tensile Strength

Features

- Nylon 12 Cable Ties provide excellent UV, chemical and moisture resistant
- Ties feature inside serrations and bent tail for quick, easy installation
- Smooth edge to prevent bundle damage
- Especially suitable in high moisture, corrosive (zinc chloride and dilute acids) environments
- Good in low temperatures
- Indoor/Outdoor applications

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No

Dimensions

Width	0.19 in
Length	25.6 in
Thickness	0.06 in
Dimension - Width mm	4.8 mm
Dimension - Width inch	0.19 in
Dimension - Length Overall	25.60 in
inch	

Dimension - L Length Overall	650 mm
mm	
Dimension - Bundle Diameter	7.30 in
Max inch	

Force Related

Tensile Strength	50 / 22 lb./Kg
Rating - Minimum Tensile	50 lb
Strength lbs	

General

Color	Black
UPC	621945469396
Trade Name	UNIRAP™
Material	NYLON 12
Series	UNIRAP™ Series

Logistics

Carton Quantity	5000
-----------------	------

Product Assets

[Catalog \[English\]](#)