



CTNT50750C0, Cable Tie, 7.5" Max Bundle, 50 Lb Tensile, Black, Nylon 12

By Burndy
Catalog # [CTNT50750C0](#)



Nylon 12 Cable Tie, Tensile strength: 50 Lbs, Color: Black, 27.60"L, 0.19"W, 7.50" Bundle Dia.

Features

- Nylon 12 Cable Ties provide excellent UV, chemical and moisture resistant
- Ties feature inside serrations and bent tail for quick, easy installation
- Smooth edge to prevent bundle damage
- Especially suitable in high moisture, corrosive (zinc chloride and dilute acids) environments
- Good in low temperatures
- Indoor/Outdoor applications

General

Catalog Number	CTNT50750C0
Color	Black
Material	NYLON 12
Rating - Minimum Tensile Strength lbs	50 lb
Tensile Strength	50 / 22 lb./Kg
Trade Name	UNIRAP™
UPC	621945469358

Dimensions

Dimension - Bundle Diameter Max inch	7.50 in
Dimension - L Length Overall mm	700 mm
Dimension - Length Overall inch	27.60 in
Dimension - Width inch	0.19 in
Dimension - Width mm	4.8 mm
Thickness	0.063 in

Certifications And Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Carton Quantity	5000
Minimum Pack Quantity	100

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50071686](#)
- [Specifications - CTNT50750C0](#)



A Hubbell brand