



CTSS100100FC304C, 304 SS Tie, 160 lb,
Full Coat, .98" Bundle

By Burndy
Catalog # [CTSS100100FC304C](#)

304 Stainless Steel UNIRAP™ Cable Tie - 160 Lb. Tensile Strength
(Fully Coated)

Features

- Meet ABS Requirements
- 304 Grade Stainless Steel
- Available in Black only
- Suitable for general purpose applications
- Smooth, rounded edges along with the polyester coating add to the safety of the installer
- Self-locking steel ball design speeds installation and locks into place at any length
- Provides a strong, durable method of cable bundling
- Available in a wide range of lengths and widths
- Halogen free low smoke polyester coating

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	FULLY COATED
----------------	--------------

Dimensions

Package Height	0.700 in
Length	3.94 in
Package Weight	0.360 lb.
Dimension - Width mm	4.6 mm
Dimension - Width inch	0.18 in
Package Length	8.500 in
Package Width	4.400 in

Dimension - L Length Overall	100 mm
mm	
Width	0.18 in
Dimension - Length Overall	3.94 in
inch	
Dimension - Bundle Diameter	0.98
Max inch	

Force Related

Rating - Minimum Tensile	160
Strength lbs	

General

Trade Name	UNIRAP™
Series	UNIRAP™ Series
UPC	781810646960
Material	304 STAINLESS STEEL
UPC 14 Digit GTIN	00781810646960

Logistics

Pallet Quantity	99999
Carton Quantity	5000

Operational

Operating Temperature Celcius	115 °C
Max	
Operating Temperature Range	-40 - 115
Celcius	
Operating Temperature Celcius	-40 °C
Min	

Product Assets

[Catalog \[English\]](#)