



CTSS100400FC304C, 304 SS Tie, Full Coat, 4.02" Bundle

By Burndy
Catalog # [CTSS100400FC304C](#)

304 Stainless Steel UNIRAP™ Cable Tie - 160 Lb. Tensile Strength (Fully Coated)

Features

- Stainless Steel Cable Tie - Fully Coated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	FULLY COATED
----------------	--------------

Dimensions

Package Height	1.000 in
Length	15.75 in
Package Weight	1.110 lb.
Dimension - Width mm	4.6 mm
Dimension - Width inch	0.18 in
Package Length	20.000 in
Package Width	4.250 in
Dimension - L Length Overall mm	400 mm
Width	0.18 in
Dimension - Length Overall inch	15.75 in

Dimension - Bundle Diameter Max inch	4.02
--------------------------------------	------

Force Related

Rating - Minimum Tensile Strength lbs	160
---------------------------------------	-----

General

Trade Name	UNIRAP™
Series	UNIRAP™ Series
UPC	781810646991
Material	304 STAINLESS STEEL
UPC 14 Digit GTIN	00781810646991

Logistics

Pallet Quantity	96000
Carton Quantity	2000

Operational

Operating Temperature Celcius Max	115 °C
Operating Temperature Range Celcius	-40 - 115
Operating Temperature Celcius Min	-40 °C

Product Assets

[Catalog \[English\]](#)