



CTSS100500FC304C, Cable Tie, 304 Stainless Steel, Fully Coated, 160 Lb Tensile

By Burndy
Catalog # [CTSS100500FC304C](#)

Fully coated stainless steel cable ties 304 grade, Tensile strength: 160 Lb, 19.68" L, 0.18" W, 5.04" Bundle Dia.

Features

- Stainless Steel Cable Tie - Fully Coated

General

Catalog Number	CTSS100500FC304C
Connector Type	FULLY COATED
Material	304 STAINLESS STEEL
Operating Temperature Celcius Max	115 °C
Operating Temperature Celcius Min	-40 °C
Operating Temperature Range Celcius	-40 - 115
Rating - Minimum Tensile Strength lbs	160
Trade Name	UNIRAP™
UPC	781810647004
UPC 14 Digit GTIN	00781810647004

Dimensions

Dimension - Bundle Diameter Max inch	5.04
Dimension - L Length Overall mm	500 mm

Dimension - Length Overall inch	19.68 in
Dimension - Width inch	0.18 in
Dimension - Width mm	4.6 mm

Certifications And Compliance

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	3000
Minimum Pack Quantity	100

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_CTSSFCPC_Lineart](#)
[Sales Drawings - 50020256](#)
[Specifications - CTSS100500FC304C](#)



A Hubbell brand