



CTSS100600FC304C, 304 SS Tie, 160 lb, 6" Bundle, Full Coat

By Burndy
Catalog # [CTSS100600FC304C](#)

304 Stainless Steel UNIRAP™ Cable Tie - 160 Lb. Tensile Strength Fully Coated)

Features

- Stainless Steel Cable Tie - Fully Coated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	FULLY COATED
----------------	--------------

Dimensions

Package Height	1.000 in
Length	23.6 in
Package Weight	1.560 lb.
Dimension - Width mm	4.6 mm
Dimension - Width inch	0.18 in
Package Length	28.000 in
Package Width	4.400 in
Dimension - L Length Overall mm	600 mm
Width	0.18 in
Dimension - Length Overall inch	23.60 in

Dimension - Bundle Diameter Max inch	6.07
--------------------------------------	------

Force Related

Rating - Minimum Tensile Strength lbs	160
---------------------------------------	-----

General

Trade Name	UNIRAP™
Series	UNIRAP™ Series
UPC	781810647929
Material	304 Stainless Steel
UPC 14 Digit GTIN	00781810647929

Logistics

Minimum Pack Quantity	100
Pallet Quantity	30000
Carton Quantity	3000

Operational

Operating Temperature Celcius Max	115 °C
Operating Temperature Range Celcius	-40 - 115
Operating Temperature Celcius Min	-40 °C

Product Assets

[Catalog \[English\]](#)