



CTSS225300304C, 304 SS Tie, 225 lb  
Tensile, 3" Bundle

By Burndy  
Catalog # [CTSS225300304C](#)

304 Stainless Steel UNIRAP™ Cable Tie - 225 Lb. Tensile Strength  
(Uncoated)

Features

- Smooth, rounded edges help ensure safe, efficient handling
- Ergonomically designed installation tools consistently tensions and cuts off ties leaving flush edges
- Flame retardant and non-toxic for applications where safety from fire is critical

Specifications

|                               |    |
|-------------------------------|----|
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Standards - RoHS Compliance   | CM |
| Status                        |    |
| Certification - cULus         | No |
| UL Listed                     | No |
| Certification - CSA Approved  | No |

Configuration

|                |          |
|----------------|----------|
| Connector Type | UNCOATED |
|----------------|----------|

Dimensions

|                                 |           |
|---------------------------------|-----------|
| Package Height                  | 0.800 in  |
| Length                          | 11.81 in  |
| Package Weight                  | 0.780 lb. |
| Dimension - Width mm            | 4.6 mm    |
| Dimension - Width inch          | 0.18 in   |
| Package Length                  | 16.250 in |
| Package Width                   | 4.100 in  |
| Dimension - L Length Overall mm | 300 mm    |
| Width                           | 0.18 in   |
| Dimension - Length Overall inch | 11.81 in  |

|                             |      |
|-----------------------------|------|
| Dimension - Bundle Diameter | 3.00 |
| Max inch                    |      |

Force Related

|                                       |     |
|---------------------------------------|-----|
| Rating - Minimum Tensile Strength lbs | 225 |
|---------------------------------------|-----|

General

|                   |                     |
|-------------------|---------------------|
| Trade Name        | UNIRAP™             |
| Series            | UNIRAP™ Series      |
| UPC               | 781810651384        |
| Material          | 304 Stainless Steel |
| UPC 14 Digit GTIN | 00781810651384      |

Logistics

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 100   |
| Pallet Quantity       | 99999 |
| Carton Quantity       | 3600  |

Operational

|                                        |           |
|----------------------------------------|-----------|
| Operating Temperature Celcius          | 300 °C    |
| Max                                    |           |
| Operating Temperature Range Celcius    | -40 - 300 |
| Operating Temperature Celcius          | -40 °C    |
| Min                                    |           |
| Operating Temperature Range Fahrenheit | -         |

Product Assets

[Catalog \[English\]](#)



A Hubbell brand