



CTSS225500304C, 304 SS Tie, 225 lb
Tensile, 5.04" Bundle

By Burndy
Catalog # [CTSS225500304C](#)

304 Stainless Steel UNIRAP™ Cable Tie - 225 Lb. Tensile Strength
(Uncoated)

Features

- Smooth, rounded edges help ensure safe, efficient handling
- Ergonomically designed installation tools consistently tensions and cuts off ties leaving flush edges
- Flame retardant and non-toxic for applications where safety from fire is critical

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	UNCOATED
----------------	----------

Dimensions

Package Height	0.800 in
Length	19.68 in
Package Weight	1.190 lb.
Dimension - Width mm	4.6 mm
Dimension - Width inch	0.18 in
Package Length	26.500 in
Package Width	4.700 in
Dimension - L Length Overall mm	500 mm
Width	0.18 in
Dimension - Length Overall inch	19.68 in

Dimension - Bundle Diameter	5.04
Max inch	

Force Related

Rating - Minimum Tensile Strength lbs	225
---------------------------------------	-----

General

Trade Name	UNIRAP™
Series	UNIRAP™ Series
UPC	781810651407
Material	304 Stainless Steel
UPC 14 Digit GTIN	00781810651407

Logistics

Minimum Pack Quantity	100
Pallet Quantity	99999
Carton Quantity	3000

Operational

Operating Temperature Celcius	300 °C
Max	
Operating Temperature Range Celcius	-40 - 300
Operating Temperature Celcius	-40 °C
Min	
Operating Temperature Range Fahrenheit	-

Product Assets

[Catalog \[English\]](#)



A Hubbell brand