



CTSS225600304C, 304 SS Tie, 225 lb
Tensile, 6.07" Bundle

By Burndy
Catalog # [CTSS225600304C](#)

304 Stainless Steel UNIRAP™ Cable Tie - 225 Lb. Tensile Strength
(Uncoated)

Features

- Smooth, rounded edges help ensure safe, efficient handling
- Ergonomically designed installation tools consistently tensions and cuts off ties leaving flush edges
- Flame retardant and non-toxic for applications where safety from fire is critical

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	UNCOATED
----------------	----------

Dimensions

Package Height	0.600 in
Length	23.62 in
Package Weight	1.390 lb.
Dimension - Width mm	4.6 mm
Dimension - Width inch	0.18 in
Package Length	29.250 in
Package Width	4.400 in
Dimension - L Length Overall mm	600 mm
Width	0.18 in
Dimension - Length Overall inch	23.62 in

Dimension - Bundle Diameter Max inch	6.07
--------------------------------------	------

Force Related

Rating - Minimum Tensile Strength lbs	225
---------------------------------------	-----

General

Trade Name	UNIRAP™
Series	UNIRAP™ Series
UPC	781810651414
Material	304 Stainless Steel
UPC 14 Digit GTIN	00781810651414

Logistics

Minimum Pack Quantity	100
Pallet Quantity	7500
Carton Quantity	2500

Operational

Operating Temperature Celcius Max	300 °C
Operating Temperature Range Celcius	-40 - 300
Operating Temperature Celcius Min	-40 °C
Operating Temperature Range Fahrenheit	-

Product Assets

[Catalog \[English\]](#)